



Fig. 1 FX® 9003 Head protector

## Cleaning instruction for the FX® 9003 Head Protector

The FX® 9003 Head protector's scratch-resistant polycarbonate lens and shell are certified to ANSI Z87 + Sections 9 and 10 and European EN166 section 7.

For use in FX® interactive training with 9 mm, .38 cal. or 5.56 mm Simunition® FX® Marking cartridges only. DO NOT USE WITH ANY OTHER TYPE OR CALIBER OF AMMUNITION.

### Cleaning the FX 9003® Head protector

The FX® 9003 head protector cleaning procedures shall be carried out as follows:

1. Using a clean container, wash the FX® 9003 head protector in a solution of two (2) parts detergent (mild dish-hand washing liquid or equivalent) to one hundred (100) parts of water, at a temperature of (35°C/ 95°F). Agitate the FX® 9003 head protector for one (1) minute by hand. Remove the FX® 9003 head protector from the solution and drain water from the outside and inside of the Head protector.
2. Rinse the FX® 9003 head protector thoroughly with fresh and clean water and drain water from the inside and outside of mask.

### Disinfect the FX 9003® Head protector

1. Using a clean container, disinfect the FX® 9003 head protector in a solution of two (2) parts Dettol Antiseptic Disinfectant (liquid), DIN 373 435 (Chloroxylenol solution, kills germs or equivalent) to one hundred (100) parts of water, at a temperature of (35°C/ 95°F). Agitate the FX® 9003 head protector for thirty (30) seconds by hand. Remove the FX® 9003 head protector from the solution and drain the outside and inside of the Head protector.
2. Rinse the FX® 9003 head protector thoroughly with fresh and clean water and drain water from the inside and outside of mask.

### Drying the FX 9003® Head protector

1. Using a clean cloth, wipe the inside of the FX® 9003 Head protector. Make sure there is no excess moisture.
2. Wipe the lens carefully with a soft (non abrasive) dry cloth, making sure the water stains from the inside and outside surfaces of lens are removed.
3. Allow the FX® 9003 head protector to dry prior to store in storage pouch.

### Head protector storage

A storage pouch is supplied with this head protector to ensure protection of the lens. Make sure that the head protector is cleaned and dried before storing.

#### WARNING

Do not use detergents (other than the ones specified above) that may contain reactive cleaning/disinfecting chemicals such as alcohol, hydrocarbons, ammonium, etc, to clean the lens. Such chemicals may remove the manufacturer's original antiscratch/ anti-fog lens coating and/or reduce the ballistic properties of the lens.

#### NOTE

- Great care shall be taken to prevent scratching the lens surfaces.
- The storage pouch can also be washed by using the same above cleaning and disinfect procedure. The storage pouch shall be hang for drying.
- DO NOT WASH OR DRY THE FX® 9003 head protector IN THE WASHING MACHINE OR SPIN DRYER.

**WARRANTY:** General Dynamics Ordnance and Tactical Systems-Canada Inc. (GD-OTS Canada) warrants that the goods shall be free from defect in materials and workmanship during the period of three (12) months following the date of delivery. This warranty is the exclusive warranty given by GD-OTS Canada.

**LIMITATION OF WARRANTY :** Simunition® FX® 9000 Protective Head protectors series are designed for use with 9mm, .38 FX® and/or 5.56 mm FX® Marking cartridges only. Use of any other ammunition is dangerous and shall void this warranty.

# SIMUNITION®

Trademarks and registered trademarks of General Dynamics Ordnance and Tactical Systems-Canada Inc. are denoted by TM and ® respectively.

© 2012 GD-OTS Canada

Canada General Dynamics Ordnance and Tactical Systems-Canada Inc.  
5 Montée des Arsenaux, Repentigny, Québec, Canada J5Z 2P4  
Tel.: 1-450-581-5999 Fax: 1-450-581-0231  
E-mail : info@simunition.com  
Management System certified to ISO 9001, ISO 14001, OHSAS 18001

US General Dynamics Ordnance and Tactical Systems-Simunition® Operations  
P. O. Box 576, Avon, CT 06001-0576 USA  
Toll free US only : 1-800-465-8255 ; 1-860-404-0162 Fax: 1-860-404-0169  
E-mail : info@simunition.com

Web site www.simunition.com

8972120\_Cleaning process\_REV0